



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 250V



## Features & Benefits

- Auto-ground clip assures positive ground.      WR marking on face as required by UL Standard.
- Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.      Strap tabs wrap around face to prevent strap from separating from face and back body.
- Tri-drive brass terminal screws.      Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for more wiring flexibility.      Heavy-duty, brass strap for added strength and ground conductivity.
- UV-resistant nylon face for longer life under adverse environmental conditions.      Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.      .032 inch thick brass triple-wipe power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).      For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                    |                |                   |               |
|--------------------|----------------|-------------------|---------------|
| Product Line       | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Commercial     | Standard          | UL 498        |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

### Listing Agencies / 3rd Party Agencies

---

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

---

#### Technical Information

---

|       |       |                 |   |
|-------|-------|-----------------|---|
| Phase | Three | Number of Wires | 3 |
|-------|-------|-----------------|---|

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

---

|           |             |         |         |
|-----------|-------------|---------|---------|
| Wire Size | 14 - 10 AWG | Voltage | 250.0 V |
|-----------|-------------|---------|---------|

---